

Garant GRIDLINE

**Roller cabinet with drawers 75 kg, 46×24G, Height mm / number of drawers: 885/8****Order data**

Order number	931425 885/8
GTIN	4062406352738
Item class	9GK

**Description****Version:****Complete with drawers 46×24G.**

Roller cabinet in 50×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

**100% full extension drawers** with differential runners. Drawers with slots at 50-mm/2G intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport.

Absolutely necessary for all roller cabinets.

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Only GridLine divider inserts can be used in the widths 2G, 4G, 6G, 8G, 10G or 12 G.

**Technical description**

Drawer body usable height	600 mm
Drawer usable depth	600 mm

Electronic locking system can be retrofitted	yes
Wheel Ø	125 mm
Individual drawer release system	One-hand
Treadless tyres	yes
ComfortClose	no
Number of fixed wheels without parking brake	2
Usable height	600 mm
Width	1250 mm
Drawer/pull-out shelf load capacity	75 kg
Height	885 mm
Weight	217 kg
Number of castors with parking brake	2
Drawer usable depth in G	24
Drawer usable width	1150 mm
Number of drawers	8
with anti-roll lip	yes
Drawer body height	700 mm
Drawer usable width in G	46
Drawer usable area in G	46×24
Depth	700 mm
maximum load capacity	600 kg
Drawer runner extension (partial/full extension)	100 %
Number of doors	0
Version	wheeled
Version	with drawers
Number of pull-out shelves	0
Usable height for drawers	600 mm
Casing open at the top	no
Material thickness	1.2 mm

Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	46x24G
Type of product	Assembly trolley

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 75 mm	931454 75
Roller cabinet for drawers Height mm / number of drawers 885/0	931427 885/0
Sheet metal cover top with raised edge on 4 sides Dimension in G 50X28	951972 50X28