

**Garant**

**"4 in 1" drilling and turning tool 1.5×D, right-hand, Ø DC: 12mm**


**Order data**

Order number	268404 12
GTIN	4062406272838
Item class	21X

**Description**
**Version:**

Plain shank.

**Application:**

1. Facing of end faces.
2. Drilling (drilling out and drilling from solid) – flat drilled hole end.
3. Internal longitudinal turning.
4. External longitudinal turning.

**Note:**

- **Choose corner radii and toolholder size as large as possible.**
- **Drilling tolerance + 0.15 mm (for drilling processes with a driven tool).**
- **When drilling greater than nominal Ø, residual material will remain.**
- **Always use internal cooling for drilling (at least 5 bar).**

**Technical description**

Nominal Ø D	12 mm
Reach L <sub>1</sub>	18 mm
Pack of insert screws	269028 41 (IP7; 0.9 Nm)
Shank Ø D <sub>s</sub>	16 mm
suitable indexable insert	ZCMX 06..
Overall length L	100 mm
Application type	right-hand
Through-coolant	yes

Type of product

Boring bar

---

## Accessories

Set of insert screws Type 41

269028 41