



LED headlamp with battery, Type: IH3



Order data

Order number	081476 IH3
GTIN	4058205000680
Item class	04B

Description

Version:

Powerful high-performance LED **industrial** headlamp for professional use.

- **Pivoting head and stepless focussing function.**
- **Exchangeable and washable head band.**

Very light-weight headband lamp, easy to operate. Easily dimmed.

Function:

IPX4: Protected against splashed water from all directions, but without any protection against foreign bodies or touching.

IP Index of Protection: IP X4

Manufacturer's designation: IH3

ATEX zone: no

Illumination: 120 lm

Illumination step 2: 5 lm

Working life: 6 h

Lighting life stage 2: 60 h

Technical description

Smart Light Technology (SLT)	no
Illumination	120 lm
chemical composition	Alkaline manganese
Rapid Focus	no
IP Index of Protection	IP X4

Lighting life stage 2	60 h
Number of batteries contained	3
Including belt pocket	no
Head Ø	28 mm
Battery type	Micro, AAA
rechargeable	no
Weight	133 g
Working life	6 h
Manufacturer's designation	iH3
Illumination step 2	5 lm
ATEX zone	no
Advanced Focus System (AFS)	yes
Power supply	Battery-powered
Type of product	Headlamp

Accessories

Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline manganese battery set International size LR3	081558 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081556 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline manganese battery set International size LR3	081557 LR3
Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline-manganese batteries International size LR3	081554 LR3