



LED headlamp with battery, Type: IH5



Order data

Order number	081476 IH5
GTIN	4058205015998
Item class	04B

Description

Version:

Powerful high-performance LED **industrial** headlamp for professional use.

- **Pivoting head and stepless focussing function.**
- **Exchangeable and washable head band.**

Innovative multi-purpose light with removable lamp head.

Flexibility in use, can be operated either with a rechargeable battery or disposable battery.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

Manufacturer's designation: IH5

ATEX zone: no

Illumination: 200 lm

Illumination step 2: 20 lm

Working life: 4.5 h

Lighting life stage 2: 35 h

Technical description

Rapid Focus	yes
Including belt pocket	no
Lighting life stage 2	35 h
IP Index of Protection	IP 54

Power supply	Battery-powered
Battery type	Mignon, AA
Weight	92 g
Head Ø	31 mm
rechargeable	no
Illumination step 2	20 lm
Smart Light Technology (SLT)	yes
Manufacturer's designation	iH5
Advanced Focus System (AFS)	yes
Number of batteries contained	1
Working life	4.5 h
chemical composition	Alkaline manganese
ATEX zone	no
Illumination	200 lm
Type of product	Headlamp

Accessories

Alkaline-manganese batteries International size LR3	081554 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline manganese battery set International size LR3	081558 LR3
Alkaline manganese battery set International size LR3	081557 LR3
Alkaline-manganese batteries International size LR3	081556 LR3