



LED headlamp with rechargeable battery, Type: IH5R



Order data

Order number	081478 IH5R
GTIN	4058205016025
Item class	04B

Description

Version:

Powerful high-performance LED **industrial** headlamp for professional use.

- **Pivoting head and stepless focussing function.**
- **Exchangeable and washable head band.**

Innovative multi-purpose light with removable lamp head.

Flexibility in use, can be operated either with a rechargeable battery or disposable battery.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

Manufacturer's designation: IH5R

ATEX zone: no

Illumination: 400 lm

Illumination step 2: 20 lm

Working life: 4 h

Lighting life stage 2: 35 h

Technical description

IP Index of Protection	IP 54
Type of rechargeable battery	Lithium-ion
Working life	4 h
Rapid Focus	yes

Data sheet

Including belt pocket	no
Smart Light Technology (SLT)	yes
Battery capacity	0.75 A·h
Battery voltage	3.7 V
Number of rechargeable batteries contained	1
Manufacturer's designation	iH5R
Head Ø	31 mm
Advanced Focus System (AFS)	yes
Power supply	Rechargeable battery-powered
Lighting life stage 2	35 h
Illumination step 2	20 lm
ATEX zone	no
Illumination range	40 - 180 m
Illumination	400 lm
Weight	98 g
Type of product	Headlamp