



## LED headlamp with rechargeable battery, Type: IH8R



### Order data

|              |               |
|--------------|---------------|
| Order number | 081478 IH8R   |
| GTIN         | 4058205010313 |
| Item class   | 04B           |

### Description

#### Version:

Powerful high-performance LED **industrial** headlamp for professional use.

- **Pivoting head and stepless focussing function.**
- **Exchangeable and washable head band.**

Powerful light-weight multi-purpose light with helmet attachment and belt bag.

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

Manufacturer's designation: IH8R

ATEX zone: no

Illumination: 600 lm

Illumination step 2: 250 lm

Illumination step 3: 10 lm

Working life: 10 h

### Technical description

|  |                              |
|--|------------------------------|
| Power supply                               | Rechargeable battery-powered |
| Illumination                               | 600 lm                       |
| Weight                                     | 158 g                        |
| Number of rechargeable batteries contained | 1                            |

|                              |             |
|------------------------------|-------------|
| Battery voltage              | 3.6 V       |
| Smart Light Technology (SLT) | yes         |
| Advanced Focus System (AFS)  | yes         |
| Lighting life stage 3        | 120 h       |
| Battery capacity             | 3.2 Ah      |
| Rapid Focus                  | yes         |
| Illumination step 3          | 10 lm       |
| Illumination range           | 20 - 150 m  |
| ATEX zone                    | no          |
| Type of rechargeable battery | Lithium-ion |
| Including belt pocket        | yes         |
| IP Index of Protection       | IP 54       |
| Illumination step 2          | 250 lm      |
| Manufacturer's designation   | iH8R        |
| Working life                 | 10 h        |
| Head Ø                       | 36 mm       |
| Lighting life stage 2        | 15 h        |
| Type of product              | Headlamp    |