



LED headlamp with rechargeable battery, Type: IH9R



Order data

Order number	081478 IH9R
GTIN	4058205015967
Item class	04B

Description

Version:

Powerful high-performance LED **industrial** headlamp for professional use.

- **Pivoting head and stepless focussing function.**
- **Exchangeable and washable head band.**

Flexibility in use, can be operated either with a rechargeable battery or disposable battery.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

IP Index of Protection: IP 54

Manufacturer's designation: IH9R

ATEX zone: no

Illumination: 400 lm

Illumination step 2: 170 lm

Illumination step 3: 20 lm

Light current boost: 600 lm

Technical description

Working life	7 h
Battery voltage	3.7 V
IP Index of Protection	IP 54

Data sheet

Manufacturer's designation	iH9R
Weight	139 g
Type of rechargeable battery	Lithium-ion
Including belt pocket	no
Illumination step 2	170 lm
Illumination range	40 - 200 m
Illumination step 3	20 lm
ATEX zone	no
Lighting life stage 2	10 h
Power supply	Rechargeable battery-powered
Lighting life stage 3	60 h
Head Ø	31 mm
Advanced Focus System (AFS)	yes
Battery capacity	1.55 A·h
Number of rechargeable batteries contained	1
Illumination	400 lm
Rapid Focus	yes
Smart Light Technology (SLT)	yes
Light current boost	600 lm
Type of product	Headlamp