



Angled die grinder Cordless, Type: M12FDGA422



Order data

Order number	077257 M12FDGA422
GTIN	4058546290672
Item class	03L

Description

Version:

FUEL™ cordless **angled** die grinder in compact design (overall length 119 mm). **DRIVE-CONTROL** 4-speed setting and sensitive speed controller for good control.

Supplied with:

1 pc. 2.0 / 1 pc. 4.0 Ah battery packs, C12 C charger, 1 pc. each of collet 6 mm and 8 mm, tool bag.

Note:

Suitable grinding discs (CER) can be found from No. 554012, for cleaning discs and coarse cleaning discs see No. 554050; 554051; 554054 and 554055.

Technical description

Weight	0.8 kg
Battery capacity	2 Ah
Battery capacity	4 Ah
Speed range	0 - 24500 min ⁻¹
Number of rechargeable batteries contained	2

Type of rechargeable battery	Lithium-ion
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Battery voltage	12 V
maximum collet Ø	6 - 8 mm
Manufacturer's designation	M12FDGA-422B
maximum disc Ø	50 mm
Power supply	Rechargeable battery-powered
Type of product	Straight die grinder

Accessories

Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
Cleaning disc (A) Fleece version FINE	554055 FINE
Fleece abrasive finishing disc Grit equivalent 180	554042 180
Coarse cleaning disc (SiC) Fleece version CRS	554051 CRS
Battery charger Type M1218C	073840 M1218C
Wheel brush with shank Brass wire 0.20 mm. Brush Ø D1× bristle width L1 30X6 mm	574350 30X6
Battery charger Type M1218FC	073840 M1218FC
Battery starter set Type M12NRG4	073839 M12NRG4
Cleaning disc (A) Fleece version MED	554055 MED
Coarse cleaning disc (SiC) Fleece version CRS	554050 CRS
Cleaning disc (A) Fleece version FINE	554054 FINE
Wheel brush with shank Steel wire 0.30 mm Brush Ø D1× bristle width L1 30X6 mm	574000 30X6
Rubber backing pad shank Ø 6 mm medium hard External Ø 50 mm	554093 50
Li-ion system M12B6 Battery type MB12	073829 MB12
Fleece abrasive finishing disc Grit equivalent 280	554042 280
Li-ion system M12B4 Battery type MB12	073815 MB12

Fleece abrasive finishing disc Grit equivalent 100	554042 100
Rubber backing pad shank Ø 6 mm medium hard External Ø 75 mm	554093 75
Cleaning disc (A) Fleece version MED	554054 MED