



Straight die grinder Cordless, Type: M12FDGS422



Order data

Order number	077258 M12FDGS422
GTIN	4058546290641
Item class	03L

Description

Version:

FUEL™ cordless straight die grinder (overall length 262 mm). **DRIVE-CONTROL** 3-speed setting.

Supplied with:

1 pc. 2.0 / 1 pc. 4.0 Ah battery packs, C12 C charger, 1 pc. each of collet 6 mm and 8 mm, tool bag.

Note:

Suitable grinding discs (CER) can be found from No. 554012, for cleaning discs and coarse cleaning discs see No. 554050; 554051; 554054 and 554055.

Technical description

Manufacturer's designation	M12FDGS-422B
Number of rechargeable batteries contained	2
Weight	1 kg
maximum collet Ø	6 - 8 mm
Battery capacity	2 Ah
Battery capacity	4 Ah
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Type of rechargeable battery	Lithium-ion
Speed range	0 - 21000 min ⁻¹
Battery voltage	12 V
maximum disc Ø	50 mm

Power supply	Rechargeable battery-powered
Type of product	Straight die grinder

Accessories

Fleece abrasive finishing disc Grit equivalent 100	554043 100
Fleece abrasive finishing disc Grit equivalent 100	554042 100
Fleece abrasive finishing disc Grit equivalent 280	554043 280
Cleaning disc (A) Fleece version MED	554054 MED
Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
Li-ion system M12B4 Battery type MB12	073815 MB12
Rubber backing pad shank Ø 6 mm medium hard External Ø 50 mm	554093 50
Fleece abrasive finishing disc Grit equivalent 180	554043 180
Cleaning disc (A) Fleece version FINE	554055 FINE
Wheel brush with shank Brass wire 0.20 mm. Brush Ø D1× bristle width L1 30X6 mm	574350 30X6
Coarse cleaning disc (SiC) Fleece version CRS	554051 CRS
Fleece abrasive finishing disc Grit equivalent 280	554042 280
Coarse cleaning disc (SiC) Fleece version CRS	554050 CRS
Li-ion system M12B6 Battery type MB12	073829 MB12
Fleece abrasive finishing disc Grit equivalent 180	554042 180
Battery starter set Type M12NRG4	073839 M12NRG4
Rubber backing pad shank Ø 6 mm medium hard External Ø 75 mm	554093 75
Cleaning disc (A) Fleece version FINE	554054 FINE
Cleaning disc (A) Fleece version MED	554055 MED
Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC
	574000 30X6

Wheel brush with shankSteel wire 0.30 mm Brush \varnothing D1×
bristle width L1 30X6 mm
