



## Angle grinder Deadman, Type: AGVKB24



### Order data

Order number	077162 AGVKB24
GTIN	4058546293628
Item class	03M

### Description

#### Version:

#### Powerful 230 mm angle grinder:

- **Dust-proof PROtector motor with smooth start-up and inrush current limitation.**
- **Safeguard against accidental restart.**
- **Vibration-damped adjustable additional handle.**
- **Spindle locking pin.**

Version with dead-man's switch, which switches the machine off immediately the trigger is released. Angle grinder with **RAPIDSTOP™** brake and safety shut-off.

Removable dust hood protects against contamination and extends the lifetime of the motor.

#### Supplied with:

Supplied with protective hood, additional handle. FIXTEC quick-clamping nut.

### Technical description

Weight	5.9 kg
maximum vibration to EN	2.7 m/s <sup>2</sup>
Power consumption	2400 W
Dead man's circuit	yes
Special features	FIXTEC
Special features	Dead man's switch
Manufacturer's designation	AGVKB-24-230 EKX DMS

Soft start	yes
maximum speed	6500 min <sup>-1</sup>
maximum cutting depth	68 mm
Restart block	yes
maximum disc Ø	230 mm
Power supply	Mains operated
Type of product	Angle grinder