



Cordless circular saw, Type: M18FCSG66



Order data

| | |
|--------------|------------------|
| Order number | 078207 M18FCSG66 |
| GTIN | 4058546288235 |
| Item class | 03L |

Description

Version:

- **Metal hook for simple and secure suspension of the unit.**
- **Cold cutting without burrs or sparks.**
- **Depth of cut setting, no tools required, for cuts 1 to 57 mm deep.**

Cordless portable circular saw delivers performance identical to an equivalent cable unit – up to 750 cuts in 90 × 45 mm softwood on one battery charge (M18™ 12 Ah). Compatible with guide rail (No. 078208 GRU1400).

- **Brushless POWERSTATE™ motor for higher cutting speeds.**
- **REDLINK PLUS™ electronics with digital overload protection, for more power.**

Supplied with:

Supplied with M12-18FC charger, carrying case.

Note:

See from No. 073814 and No. 073839 for suitable spare batteries and starter kits. For a suitable circular saw blade see from No. 584075.

Technical description

| | |
|------------------|-------|
| Weight | 10 kg |
| Saw blade bore Ø | 30 mm |
| Battery capacity | 12 Ah |

| | |
|--|------------------------------|
| Version | Hand-held circular saw |
| maximum vibration to EN | <2.5 m/s ² |
| Number of rechargeable batteries contained | 1 |
| Type of rechargeable battery | Lithium-ion |
| maximum cutting depth 90° | 66 mm |
| suitable battery - supplier / battery type / voltage | Milwaukee type B 18 V |
| Packaging | Modular case (HD=Heavy Duty) |
| Manufacturer's designation | M18FCSG66-121C |
| Saw blade Ø | 190 mm |
| maximum speed | 5800 min ⁻¹ |
| Battery voltage | 18 V |
| Power supply | Rechargeable battery-powered |
| Type of product | Saw |

Accessories

| | |
|--|------------------|
| Circular saw blade, wood, alternating teethuniversal Blade Ø D 190 mm | 584075 190 |
| Battery starter setHigh Output™ Battery type M18HNRG3 | 073826 M18HNRG3 |
| Circular saw blade, wood, alternating teethuniversal Blade Ø D 160 mm | 584075 160 |
| Li-ion batteryHigh Output™ Battery type MHB12 | 073811 MHB12 |
| Battery starter setHigh Output™ Type M18HNRG8 | 073831 M18HNRG8 |
| Battery starter setHigh Output™ Type M18HNRG55 | 073830 M18HNRG55 |
| Battery starter setHigh Output™ Type M18HNRG12 | 073833 M18HNRG12 |
| Li-ion batteryHigh Output™ Battery type MHB55 | 073809 MHB55 |
| Battery starter set Type M18NRG5 | 073839 M18NRG5 |
| Circular saw blade, wood, alternating teethuniversal Blade Ø D 230 mm | 584075 230 |
| | 584075 210 |

Circular saw blade, wood, alternating teethuniversal Blade
Ø D 210 mm

Li-ion system M18B2 Battery type MB18

073827 MB18

Li-ion system M18B5 Battery type MB18

073816 MB18

Circular saw blade, wood, alternating teethuniversal Blade
Ø D 300 mm

584075 300

Circular saw blade, wood, alternating teethuniversal Blade
Ø D 250 mm

584075 250

Circular saw blade, wood, alternating teethuniversal Blade
Ø D 350 mm

584075 350

Li-ion batteryHigh Output™ Battery type MHB8

073810 MHB8

Li-ion batteryHigh Output™ Battery type MHB3

073808 MHB3