



## Cordless hammer drill / driver, Type: GSB1215B



### Order data

Order number	070104 GSB1215B
GTIN	3165140995955
Item class	03B

### Description

#### Version:

**Bosch cordless hammer drill / driver** for very heavy-duty screwdriving, drilling and hammer drilling applications.

- **Electronic Cell Protection (ECP) protects the battery against overheating and deep discharge.**
- **Electronic Motor Protection (EMP) protects the motor against overloading.**
- **Mechanical multi-stage torque cut-out.**
- **Handy belt clip (not 070104).**
- **Integral LED light, battery charge indicator.**
- **Quick-clamping drill chuck.**

Sturdy and handy cordless drill / driver, only **1 kg** in weight.

#### Supplied with:

Supplied with 2× Li-ion batteries, charger and transport bag.

#### Note:

See from No. 073851 and 073866 for suitable replacement batteries and chargers.

### Technical description

Type of rechargeable battery	Lithium-ion
------------------------------	-------------

Quick-clamping chuck range	1 - 10 mm
Weight	1 kg
Battery capacity	2 Ah
maximum twist drill size Ø in wood	19 mm
maximum torque soft	15 Nm
maximum twist drill size Ø in steel	10 mm
maximum speed 2nd speed	1300 min <sup>-1</sup>
Motor design	Motor with brushes
Manufacturer's designation	GSB 12V-15
maximum vibration to EN with hammer drill function	10.5 m/s <sup>2</sup>
typical application	Medium
maximum speed 1st speed	0 - 380 min <sup>-1</sup>
maximum vibration to EN without hammer drill function	<2.5 m/s <sup>2</sup>
maximum torque hard	30 Nm
suitable battery - supplier / battery type / voltage	Bosch 12 V
Battery voltage	12 V
maximum twist drill size Ø in concrete	10 mm
Number of rechargeable batteries contained	2
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Concrete
Suitable for material	Steel
Suitable for material	Stone
Suitable for material	Masonry
Type of product	limpact drill /screwdriver

## Accessories

Battery charger Type GAL1240	073866 GAL1240
Li-ion battery Battery type, battery voltage B12 V	073851 B12