

**Cordless hammer drill / driver ProCORE, Type: GSB1860PC****Order data**

Order number	070106 GSB1860PC
GTIN	3165140956352
Item class	03B

Description**Version:**

Bosch cordless hammer drill / driver for very heavy-duty screwdriving, drilling and hammer drilling applications.

- **Electronic Cell Protection (ECP) protects the battery against overheating and deep discharge.**
- **Electronic Motor Protection (EMP) protects the motor against overloading.**
- **Mechanical multi-stage torque cut-out.**
- **Handy belt clip (not 070104).**
- **Integral LED light, battery charge indicator.**
- **Quick-clamping drill chuck.**

With **brushless EC motor**.

Kick-back control with automatic shut-down if jammed, together with unique precision clutch.

Compact design, very short head length (only 184 mm) for perfect handling (size GSB1860PC), therefore ideal for working in restricted spaces. Can be retrofitted with a connectivity module.

With motor brake.

Supplied with:

Supplied with 2× ProCORE 18V 4.0 Ah Li-ion batteries, charger and L-BOXX.

Note:

See from No. 073851 and 073866 for suitable replacement batteries and chargers.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Manufacturer's designation: GSB 18V-60 PC

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 4 A·h

Battery voltage: 18 V

Motor design: Brushless motor

Technical description

maximum speed 2nd speed	1900 min ⁻¹
maximum twist drill size Ø in steel	10 mm
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
maximum vibration to EN without hammer drill function	2.5 m/s ²
maximum speed 1st speed	0 - 600 min ⁻¹
Manufacturer's designation	GSB 18V-60 PC
Weight	1.9 kg
maximum twist drill size Ø in concrete	10 mm
maximum torque soft	31 N·m
maximum torque hard	60 N·m
maximum vibration to EN with hammer drill function	8 m/s ²
Quick-clamping chuck range	1.5 - 13 mm
Motor design	Brushless motor
typical application	Strong
Battery capacity	4 A·h
maximum twist drill size Ø in wood	38 mm
Battery voltage	18 V
Packaging	Modular case (L-Boxx)
suitable battery - supplier / battery type / voltage	Bosch 18 V
Power supply	Rechargeable battery-powered
Suitable for material	Concrete

Suitable for material	wood
Suitable for material	Steel
Suitable for material	Masonry
Type of product	limpact drill /screwdriver

Accessories

Li-ion battery ProCore Battery type, battery voltage C18 V	073856 C18
--	------------