

**Cordless drill / driver, Type: GSR1215B****Order data**

Order number	070240 GSR1215B
GTIN	3165140895248
Item class	03B

Description**Version:**

Bosch cordless drill / driver

- **Compact, powerful 12 V cordless drill with forward/reverse operation.**
- **With Electronic Motor Protection (EMP) and Electronic Cell Protection (ECP).**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Advantage:

Compact design ideal for restricted places.

Supplied with:

Supplied with charger and transport bag. 2 x 12V / 2.0 Ah Li-ion rechargeable batteries

Note:

Suitable spare batteries and chargers can be found under No. 073851 – 073866.

Technical description

Quick-clamping chuck range	0 - 10 mm
----------------------------	-----------

Battery capacity	2 Ah
Number of rechargeable batteries contained	2
suitable battery - supplier / battery type / voltage	Bosch 12 V
Weight	1 kg
maximum twist drill size Ø in steel	10 mm
Speed range 1st speed	0 - 380 min ⁻¹
Manufacturer's designation	GSR 12V-15
Type of rechargeable battery	Lithium-ion
typical application	Medium
Speed range 2nd speed	0 - 1300 min ⁻¹
maximum twist drill size Ø in wood	19 mm
Motor design	2-pole motor
maximum torque hard	30 Nm
maximum torque soft	15 Nm
maximum vibration to EN	<2.5 m/s ²
Battery voltage	12 V
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/driver
USP1	12V, 2-pole motor
USP2	Quick-change chuck clamping range 0-10, with softgrip, with battery charge display

Accessories

Li-ion battery Battery type, battery voltage B12 V	073855 B12
Battery charger Type 1880CV	073866 1880CV

Li-ion battery Battery type, battery voltage B12 V	073851 B12
Battery charger Type GAL18160C	073866 GAL18160C
Li-ion battery Battery type, battery voltage B12 V	073859 B12