

**Cordless drill / driver ProCORE, Type: GSR18110C****Order data**

Order number	070245 GSR18110C
GTIN	4059952525419
Item class	03B

**Description****Version:**

- **Compact, powerful cordless drill with forward/reverse operation.**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

**Kick-back control** with automatic shut-down if jammed, together with unique precision clutch and motor brake. 13 mm auto-lock metal drill chuck. High torque.

Can be retrofitted with a **connectivity** module.

**Advantage:**

Solid metal drill chuck.

**Supplied with:**

Supplied with 2× Li-ion batteries, quick charger and L-BOXX.

**Note:**

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

**Technical description**

maximum twist drill size Ø in steel	13 mm
Interface	Bluetooth interface
Speed range 2nd speed	0 - 2100 min <sup>-1</sup>
Packaging	Modular case (L-Boxx)
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum torque hard	110 Nm
maximum vibration to EN	<2.5 m/s <sup>2</sup>
Motor design	Brushless motor
Battery capacity	4 Ah
Weight	2.2 kg
typical application	Heavy Duty
maximum twist drill size Ø in wood	82 mm
Number of rechargeable batteries contained	2
maximum torque soft	47 Nm
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Speed range 1st speed	0 - 480 min <sup>-1</sup>
Quick-clamping chuck range	1.5 - 13 mm
Manufacturer's designation	GSR 18V-110C
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Suitable for material	wood
Type of product	Drill/driver
USP1	18V
USP2	Brushless motor, quick-change chuck clamping range 1.5-13, in L-Boxx

## Accessories

Battery starter setProCore Battery type, battery voltage C18 V	073863 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073856 C18