

**Cordless angle grinder GWS, Type: 18V-10SC****Order data**

Order number	077120 18V-10SC
GTIN	3165140960915
Item class	03C

Description**Version:**

Powerful **18 V cordless angle grinder**.

- **30% more power and 125% longer run time thanks to the new EC motor and the new ProCORE 18-V battery technology.**
- **Increased safety thanks to the intelligent brake system which shortens the brake time by up to 70% and KickBack Control.**
- **User comfort thanks to keyless disc change.**

Supplied with:

Including 2 pcs. ProCORE18 V 8.0 Ah, mounting flange, GAL 1880 CV quick charger, quick clamping nut, 1 pc. Bluetooth® Low Energy Module GCY 42 Professional, safety guard, L-BOXX, 1/1 L-BOXX inlay for device and charger, additional vibration control handle.

Note:

See No. 073851 – 073866 for suitable rechargeable batteries and chargers.

Technical description

Kick-back stop	yes
Type of rechargeable battery	Lithium-ion
Soft start	no
suitable battery - supplier / battery type / voltage	Bosch 18 V

Data sheet

maximum cutting depth	34 mm
Number of rechargeable batteries contained	2
maximum vibration to EN	6 m/s ²
Battery capacity	8 Ah
Overload protection	yes
Dead man's circuit	no
Manufacturer's designation	GWS18V-10SC
maximum disc Ø	125 mm
Battery voltage	18 V
Restart block	yes
maximum speed	9000 min ⁻¹
Weight	2 kg
Packaging	Modular case (L-Boxx)
Power supply	Rechargeable battery-powered
Type of product	Angle grinder

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/077120-18V-10SC>