



Pair of heat resistant gloves, Glove size: 10



Order data

Order number	094645 10
GTIN	4062406273316
Item class	02H

Description

Version:

HOLEX heat-resistant gloves with fire-resistant 10-gauge knit, ideal for working on hot parts.

Standard:

EN 388; EN 407; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Accuracy of fit	very good
silicone-free	yes
Touch sensitivity	good
Oil grip	medium
Cold protection	not available
EN 388 tear propagation resistance	2

Glove size	10
Material of coating	Neoprene
EN 388 abrasion resistance	2
EN 388 cut resistance	1
Wet grip	medium
EN 388 penetration resistance	3
Heat protection	very good
Type of glove	Heat protection gloves
Protection category	Category III
Glove characteristics	Flame resistance stage 4
EN 388	2131X
EN 407	4231XX
Contact heat up to	250 °C
Radiated heat up to	4231XX °C
Backing material	Acrylic
Coating	Neoprene
Coating variant	The palms of the hands
Colour	black
Application	reusable
Application range	All-round
Knitted technology	10G
Heat protection up to	250 °C
Standard	EN 407
Type of product	Heat protection gloves