

Garant GRIDLINE

## Tool cabinet complete with drawers 75 kg, 36×20G, Height mm / number of drawers: 800/7



### Order data

Order number	930705 800/7
GTIN	4062406273651
Item class	9GK

### Description

#### NOTE: Colour selection possible

#### Version:

Completely equipped tool cabinet in 40×24G, with drawers 36×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

#### Fitted with:

Drawer front height, mm: 50, 75, 100, 100, 100, 125, 150

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable area in G: 36×20

Height: 800 mm

Width: 1000 mm

Depth: 600 mm

Usable height: 700 mm

Usable height for drawers: 700 mm

Drawer usable width: 900 mm

## Technical description

Drawer usable width	900 mm
Width	1000 mm
Drawer usable depth in G	20
Electronic locking system can be retrofitted	yes
Weight	149 kg
Number of drawers	7
Number of doors	0
Drawer usable depth	500 mm
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	125 mm
Drawer front height	150 mm
Usable height for drawers	700 mm
Height	800 mm
Usable height	700 mm
Drawer usable area in G	36×20
Depth	600 mm
Drawer usable width in G	36
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %

Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×20G
Type of product	Tool cabinet

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
Tool cabinet casing for drawers Height 800 mm	930735 800
Drawer, 75 kg Drawer front height 100 mm	930743 100
Drawer, 75 kg Drawer front height 125 mm	930743 125
Drawer, 75 kg Drawer front height 150 mm	930743 150
Drawer, 75 kg Drawer front height 50 mm	930743 50
Drawer, 75 kg Drawer front height 75 mm	930743 75