

Garant GRIDLINE

Tool cabinet complete with drawers 200 kg, 36×20G, Height mm / number of drawers: 800/6



Order data

Order number	930715 800/6
GTIN	4062406273743
Item class	9GK

Description

Version:

Completely equipped tool cabinet in 40×24G, with drawers 36×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

Fitted with:

Drawer front height, mm: 75, 75, 100, 100, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Number of drawers	6
Drawer usable depth in G	20

Height	800 mm
Drawer usable depth	500 mm
Usable height for drawers	700 mm
Drawer usable width in G	36
Width	1000 mm
Usable height	700 mm
Electronic locking system can be retrofitted	yes
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	150 mm
Drawer front height	200 mm
Number of doors	0
Depth	600 mm
Drawer usable area in G	36×20
Depth in units	700
Drawer usable width	900 mm
Weight	137 kg
Number of pull-out shelves	0
Base cabinet underneath height-adjustable workstation	no
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×20G

Type of product

Tool cabinet

Accessories

Drawer,200 kg Drawer front height 75 mm	930745 75
Lock plate for GridLine Type HU21	914227 HU21
Drawer,200 kg Drawer front height 200 mm	930745 200
Drawer,200 kg Drawer front height 150 mm	930745 150
Drawer,200 kg Drawer front height 100 mm	930745 100
Tool cabinet casing for drawers Height 800 mm	930735 800