

Garant GRIDLINE

## Tool cabinet complete with drawers 200 kg, 26×24G, Height mm / number of drawers: 1250/10



### Order data

Order number	931115 1250/10
GTIN	4062406352608
Item class	9GK

### Description

#### NOTE: Colour selection possible

#### Version:

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

#### Fitted with:

Drawer front height, mm: 50, 75, 75, 100, 100 125, 125, 150, 150, 200

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable area in G: 26×24

Height: 1250 mm

Width: 750 mm

Depth: 700 mm  
 Usable height: 1150 mm  
 Usable height for drawers: 1150 mm  
 Drawer usable width: 650 mm

## Technical description

Weight	197 kg
Drawer usable depth	600 mm
Drawer usable width in G	26
Usable height	1150 mm
ComfortClose	no
Electronic locking system can be retrofitted	yes
Drawer usable area in G	26×24
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	125 mm
Drawer front height	125 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	200 mm
Width	750 mm
Drawer usable depth in G	24
Depth	700 mm
Number of drawers	10
Drawer usable width	650 mm
Usable height for drawers	1150 mm
Number of doors	0

Ribbed rubber inlay with anti-roll lip on 3 sides	no
Height	1250 mm
Number of pull-out shelves	0
Base cabinet underneath height-adjustable workstation	no
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Tool cabinet

## Accessories

Drawer, 200 kg Drawer front height 75 mm	931165 75
Drawer, 200 kg Drawer front height 100 mm	931165 100
Drawer, 200 kg Drawer front height 200 mm	931165 200
Drawer, 200 kg Drawer front height 150 mm	931165 150
Drawer, 200 kg Drawer front height 125 mm	931165 125
Lock plate for GridLine Type HU21	914227 HU21
Drawer, 75 kg Drawer front height 50 mm	931163 50
Tool cabinet casing for drawers Height 1250 mm	931155 1250