

**TubiX® pipe cutter with quick adjustment, for Ø to: 35mm****Order data**

Order number	818380 35
GTIN	4003773084907
Item class	86A

Description**Version:**

Lightweight and long-lasting metal housing of magnesium, with needle bearing guide rollers and cutter wheel. Manual deburrer can be retracted into the body. Supplied with spare cutter wheel.

Advantage:

Automatic stop and clamping on to the pipe by **QuickLock quick adjustment**.

· **Quick and precise positioning of the cutter wheel on different pipe diameters.**

Application:

General purpose for cutting **copper, aluminium, and thin-walled stainless steel pipes** (up to 2 mm wall thickness).

Spare part:

For spare cutter wheel with needle bearing and quick-change pivot pin, see No. 818385.

Technical description

Cutter wheel width	6.2 mm
Cutter wheel bore	7.8 mm
for pipe outer Ø	6 - 35 mm
Cutter wheel Ø	20 mm
Manufacturer's designation	TubiX
Weight	375 g

Length	180 mm
Width	65 mm
Height	40 mm
Type of product	Pipe cutters

Accessories

Spare cutter wheel Type 1	818385 1
---------------------------	----------