



## Corner pipe wrench with S-form jaws, Pipe Ø: 2in



### Order data

Order number	810745 2
GTIN	4003773014263
Item class	86A

### Description

**Version:**

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

**KNIPEX** with S-form jaws for 3-point pipe support.

**Material:**

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

### Technical description

Jaw capacity	70 mm
Pipe Ø	2 in
overall length	540 mm
Jaw angle	45 degrees
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
S-jaw	yes
Swedish profile	yes
Type of product	Pipe wrench and water pump pliers

