



## Corner pipe wrench with S-form jaws, Pipe Ø: 1.1/2in



### Order data

Order number	810745 1.1/2
GTIN	4003773014256
Item class	86A

### Description

#### Version:

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

**KNIPEX** with S-form jaws for 3-point pipe support.

#### Material:

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

### Technical description

overall length	425 mm
Pipe Ø	1.1/2 in
Jaw capacity	60 mm
Jaw angle	45 degrees
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
S-jaw	yes
Swedish profile	yes
Type of product	Pipe wrench and water pump pliers

