



Corner pipe wrench with S-form jaws, Pipe Ø: 1 in



Order data

Order number	810745 1
GTIN	4003773014249
Item class	86A

Description

Version:

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

KNIPEX with S-form jaws for 3-point pipe support.

Material:

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

Technical description

Pipe Ø	1 in
Jaw capacity	42 mm
overall length	320 mm
Jaw angle	45 degrees
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
S-jaw	yes
Swedish profile	yes
Type of product	Pipe wrench and water pump pliers

