

HEDI

All-plastic cable drum for F, B, PL and CZ, Type: 25B2



Order data

Order number	081134 25B2
GTIN	4003644022526
Item class	08B

Description

Version:

HEDI® cable drums stand for "Made in Germany" quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches.

Sturdy cable drum of high-impact plastic with **thermal overload protection. Certified for continuous exterior use and for use in humid environments.**

- **400 V CEE input plug 16 A.**
- **1 pc. 400 V CEE output plug 16 A with self-closing cover and thermal cut-out switch.**
- **2 pcs. 250 V standard Schuko sockets with self-closing covers.**
- **Inclined 7 degrees for greater ground clearance and to make it comfortable to carry.**
- **Removable cable holder and guide for optimum cable control.**
- **Water drainage grooves.**
- **Easy to mount on a wall.**

Large and high-quality HEDI® all-plastic cable drum with a drum diameter of 290 mm and numerous ergonomic and safety features.

Folding rotary handle for individual clockwise and anticlockwise operation when winding and unwinding.

With sockets for **France, Belgium, Poland and the Czech Republic.**

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

Material cable	Armoured cable
Material of body	All-plastic
Rated power unrolled	5500 (16 A) W
Cable structure	5G2.5
Cable class	H07BQ-F
Cable length	25 m
impact-resistant and splash-proof	Category 2 (K2) to BGI
IP Index of Protection	IP 44
Nominal voltage	400 V
Power supply	Mains operated
Type of product	Cable drum