



Safety dial indicator, Measuring range / Body Ø: 0,16/58mm



Order data

Order number	432405 0,16/58
GTIN	4031452101843
Item class	46C

Description

Version:

Dimensions to DIN EN ISO 463, issue June 2006. Precision dial indicators, shockproof, safety dial indicators, shockproof, with overrun. Extremely light, robust construction, dustproof. Clamping shank Ø 8 mm h6.

Highest precision due to combined gear and lever mechanism.

Technical description

Graduation	0.001 mm
Measuring range	0.16 mm
Free stroke	4.5 mm
Gauging force	1.3 - 1.8 N
Calibration	C2
Clamping shank Ø h6	8 mm
Standard	Manufacturer's standard

Measurement variation MPE (measurement range)	2 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

CalibrationDial indicator, analogue 0.001 maximum measuring span 5 mm	023020 5
---	----------

Accessories

Dial indicator glass Type 58	432010 58
------------------------------	-----------