

**Honeywell****Pair of gloves CoreShield™ 22-7518B, Glove size: 9****Order data**

Order number	094520 9
GTIN	
Item class	09A

**Description****Version:**

**Honeywell CoreShield™ series.** The innovative light-weight cut-resistant gloves series offers **very good touch sensitivity** and pleasant freedom of movement for the fingers. In addition the series scores well for long shelf life and high sturdiness. The resilient and **breathable micro-foam coating** ensures excellent non-slip characteristics for the gloves on both oily and dry surfaces.

**CoreShield™ 22-7518B.** Cut-resistant gloves with cut protection level B and **18-gauge knitted technology** for precision work with medium cut hazards. High wearing comfort, thanks to the **HPPE** backing material.

**Standard:**

EN 388; EN 420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. The **CoreShield™ series** is available in various knitted thicknesses (10 to **18 gauge**) and coatings (nitrile micro-foam, super thin nitrile).

**Technical description**

Manufacturer's designation	CoreShield 22-7518B
----------------------------	---------------------

Contents	10
Glove characteristics	Suitable for touch screens
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	Silicone-free
Glove characteristics	DMF-free
Knitted technology	18G
Clothing standard	Oeko-Tex Standard 100
EN 388	4X31B
Backing material	HPPE
Coating	Nitrile micro-foam
Coating variant	The palms of the hands
Application range	Precision
Colour	grey / black
Weight	35-55 g
Length	220 - 270 mm
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves