

Honeywell**Pair of gloves CoreShield™ 26-0513B, Glove size: 7****Order data**

Order number	094524 7
GTIN	13603835667185
Item class	09A

Description**Version:**

Honeywell CoreShield™ series. The innovative light-weight cut-resistant gloves series offers **very good touch sensitivity** and pleasant freedom of movement for the fingers. In addition the series scores well for long shelf life and high sturdiness. The resilient and **breathable micro-foam coating** ensures excellent non-slip characteristics for the gloves on both oily and dry surfaces.

CoreShield™ 26-0513B. Cut-resistant gloves with cut protection level F for activities with extremely high cut hazards. High wearing comfort, thanks to the **HPPE-basalt fibre-metal fibre** backing material.

Standard:

EN 388; EN 420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. The **CoreShield™ series** is available in various knitted thicknesses (10 to **18 gauge**) and coatings (nitrile micro-foam, super thin nitrile).

Colour: black

Technical description

Manufacturer's designation	CoreShield 26-0513B
Contents	10
Glove characteristics	Suitable for touch screens
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	DMF-free
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	Silicone-free
Knitted technology	13G
Clothing standard	Oeko-Tex Standard 100
EN 388:2016	4X43F
Backing material	HPPE-basalt fibre-metal fibre
Coating	Nitrile micro-foam
Coating variant	The palms of the hands
Application range	All-round
Colour	black
Weight	64-96 g
Length	220 - 270 mm
Application	reusable
Cut protection class	F
Type of product	Cut-resistant gloves