

Garant GRIDLINE

**Tool cabinet complete with drawers 200 kg, 36×24G, Height mm / number of drawers: 900/6****Order data**

Order number	931315 900/6
GTIN	4062406275594
Item class	9GK

**Description****Version:**

Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

**Fitted with:**

Drawer front height, mm: 75, 100, 100, 100, 125, 300

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

**Technical description**

Weight	158 kg
--------	--------

Height	900 mm
Width	1000 mm
Electronic locking system can be retrofitted	yes
Drawer usable depth	600 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	125 mm
Drawer front height	300 mm
Usable height	800 mm
Drawer usable depth in G	24
Usable height for drawers	800 mm
Number of doors	0
Number of drawers	6
Drawer usable area in G	36×24
Depth	700 mm
Drawer usable width	900 mm
Drawer usable width in G	36
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×24G

Type of product

Tool cabinet

**Accessories**

Drawer,200 kg Drawer front height 150 mm	931355 150
Drawer,200 kg Drawer front height 100 mm	931355 100
Drawer,200 kg Drawer front height 300 mm	931355 300
Lock plate for GridLine Type HU21	914227 HU21
Drawer,200 kg Drawer front height 250 mm	931355 250
Drawer,200 kg Drawer front height 75 mm	931355 75
Drawer,200 kg Drawer front height 200 mm	931355 200
Drawer,200 kg Drawer front height 125 mm	931355 125
Tool cabinet casing for drawers Height 900 mm	931335 900