



## Rechargeable LED EX work light, Type: MIDI-EX



### Order data

Order number	081515 MIDI-EX
GTIN	5708997356111
Item class	08C

### Description

**Version:**

Explosion-proof work lamp, tested to the applicable ATEX guideline.

Extremely bright illumination and very long working life.

Rechargeable multi-function LED EX work light. Main lamp with two-stage switch and upper spotlight.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Standard:**

Certified for ATEX zone 2 and ATEX ZONE 22.

ATEX directive No. 2014/34/EU, IEC and IECEx approved and certified.

**Supplied with:**

Supplied with charging cable and charging station.

### Technical description

Power supply	Rechargeable battery-powered
Weight	180 g

IP Index of Protection	IP 65
Overall length	181 mm
ATEX zone	Zone 2
ATEX zone	Zone 22
CRI value	80
Tool properties	Suitable for EX areas
Battery capacity	1.6 Ah
Bulb	LED module
Illumination	140 - 280 lm
Overall height	29 mm
Number of rechargeable batteries contained	1
Overall width	50 mm
Battery voltage	3.8 V
Colour temperature	6500 K
Illumination time	5 h
Type of rechargeable battery	Lithium-ion
Manufacturer's designation	MIDI-EX
Type of product	Work lamp