



## Cordless hammer drill / driver, Type: M12FPDX2



### Order data

|              |                 |
|--------------|-----------------|
| Order number | 070110 M12FPDX2 |
| GTIN         | 4058546220815   |
| Item class   | 03L             |

### Description

#### Version:

- **Powerful cordless 2-speed hammer drill /screwdriver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

Compact cordless hammer drill/driver with 6-in-1 drilling system for maximum flexibility.

- **Removable drill chuck system with 3 attachments.**
- **Extremely handy thanks to the 1/4 inch hex metal bit holder under the drill chuck: only 138 mm long when the drill chuck is removed.**

#### Note:

See No. 073814 – 073816, 073827 and 073840 for suitable batteries and chargers.

The suitable Bluetooth tracking module can be found under 070103 BTT-1.

### Technical description

|  |                              |
|--|------------------------------|
| Manufacturer's designation                           | M12FPDX-202X                 |
| suitable battery - supplier / battery type / voltage | Milwaukee type B 12 V        |
| Length   | 138 mm                       |
| maximum torque                                       | 37 Nm                        |
| maximum twist drill size Ø in steel                  | 13 mm                        |
| Speed range 2nd speed                                | 0 - 1700 min <sup>-1</sup>   |
| maximum twist drill size Ø in wood                   | 35 mm                        |
| Quick-clamping chuck range                           | 1 - 13 mm                    |
| Motor design   | POWERSTATE™                  |
| Battery capacity                                     | 2 Ah                         |
| Battery voltage                                      | 12 V                         |
| Speed range 1st speed                                | 0 - 450 min <sup>-1</sup>    |
| Number of rechargeable batteries contained           | 2                            |
| Type of rechargeable battery                         | Lithium-ion                  |
| maximum twist drill size Ø in concrete               | 13 mm                        |
| Packaging  | Modular case (HD=Heavy Duty) |
| Power supply   | Rechargeable battery-powered |
| Type of product                                      | limpact drill /screwdriver   |