



769F abrasive flap disc, glass fibre pad flat, Ø 115 mm, Grit: 60



Order data

Order number	565510 60
GTIN	5902658113000
Item class	53F

Description

Version:

Coated with **precisely formed** ceramic grit mixture for **high metal removal rate and long working life**.

Application:

General grinding work with high-power angle grinders.

maximum circumferential speed: 80 m/s

Shape description: flat

Bore Ø: 22.23 mm

Technical description

Shape description	flat
Disc Ø	115 mm
Bore Ø	22.23 mm
Grit	60
Grinding media	Ceramic grit (CER)

Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
dry	suitable		