

## PRYOR

**Numeral letter punch set, 27 pieces Normal script A – Z, &, Character height: 1mm**



### Order data

Order number	085430 1
GTIN	5022044003842
Item class	08W

### Description

#### Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

**High performance precision punches**, chemically nickel-plated, very long service life.

**Normal script**; i. e. the punched character can be read directly on the component.

#### Application:

For punching into materials with a **strength up to 1200 N/mm<sup>2</sup>**.

#### Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

#### Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

### Technical description

overall length	63.5 mm
Character height	1 mm

Shank thickness	6.35
Type of product	Hand punch

---

## Accessories

Punch holder Type GRIP	085475 GRIP
------------------------	-------------