

**HOLEX****Interchangeable one-hand clamp, Jaw capacity: 600 mm****Order data**

Order number	860286 600
GTIN	4062406276614
Item class	82C

**Description****Version:**

Ergonomically shaped 2-component plastic handle, burnished rail of drawn steel. **No tools required** for conversion to spreading, thanks to intelligent release mechanism in the upper part, **reversible**. With release handle for quick adjustment.

**Application:**

General purpose use, easy to use one-handed for clamping pressures (up to 2000 N).

Cross section of the slide rail: 20×6 mm

Spreading width: 200 - 865 mm

Throat: 90 mm

**Technical description**

Jaw capacity	600 mm
Cross section of the slide rail	20×6 mm
Throat	90 mm
Spreading width	200 - 865 mm
Type of product	Clamp

