

ejendals

Pair of gloves Tegera® 8814 Infinity, Glove size: 7



Order data

Order number	094559 7
GTIN	7340118324753
Item class	04R

Description

Version:

Tegera® 8814 Infinity. The soft thin cut-resistant gloves are highly suitable for use in areas where touch screens must be used. They are **silicone-free** and offer **heat protection up to 100°C**. Thanks to the maximum cut protection class (**Cut F**) they can be used for dry work and slightly oil work with extremely high cut hazards. Dermatologically tested, and approved for handling foodstuffs.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Contents	6
Glove characteristics	Foodstuffs certified
Glove characteristics	Suitable for touch screens
Glove characteristics	Silicone-free

Knitted technology	13G
Clothing standard	Oeko-Tex Standard 100
EN 388	4X43F
EN 407	X1XXXX
Backing material	Basalt fibre, steel fibre, nylon, Spandex
Coating	Nitrile foam/water-based PU
Coating variant	The palms of the hands
Application range	All-round
Application range	Heavy Duty
Colour	grey / black
Standard	EN 407
Contact heat up to	100 °C
Application	reusable
Cut protection class	F
Type of product	Cut-resistant gloves