

## ejendals

### Pair of gloves Tegera® 8801 Infinity, Glove size: 7



#### Order data

Order number	094362 7
GTIN	7340118318677
Item class	04R

#### Description

**Version:**

**Tegera® 8801 Infinity.** Multi-purpose gloves of the Infinity range with outstanding touch sensitivity and good grip capability. Particularly thin coating with nitrile foam and water-based PU coating, suitable for dry and slightly humid working areas, with oil- and grease-resistant palms. Resistant to **contact heat up to 100 °C.**

**Standard:**

EN 388; EN ISO 21420

EN 407

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

#### Technical description

Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	6
Glove characteristics	Foodstuffs certified

EN 388	4121X
EN 407	X1XXXX
Backing material	Nylon Spandex
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	Precision
Colour	black / yellow
Knitted technology	15G
Standard	EN 407
Contact heat up to	100 °C
Application	reusable
Type of product	Multi-purpose gloves