

ejendals

Pair of gloves Tegera® 8801 Infinity, Glove size: 8



Order data

Order number	094362 8
GTIN	7340118318684
Item class	04R

Description

Version:

Tegera® 8801 Infinity. Multi-purpose gloves of the Infinity range with outstanding touch sensitivity and good grip capability. Particularly thin coating with nitrile foam and water-based PU coating, suitable for dry and slightly humid working areas, with oil- and grease-resistant palms. Resistant to **contact heat up to 100 °C.**

Standard:

EN 388; EN ISO 21420

EN 407

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	6
Glove characteristics	Foodstuffs certified

EN 388	4121X
EN 407	X1XXXX
Backing material	Nylon Spandex
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	Precision
Colour	black / yellow
Knitted technology	15G
Standard	EN 407
Contact heat up to	100 °C
Application	reusable
Type of product	Multi-purpose gloves