

ejendals

Pair of gloves Tegera® 8801 Infinity, Glove size: 9



Order data

| | |
|--------------|---------------|
| Order number | 094362 9 |
| GTIN | 7340118318691 |
| Item class | 04R |

Description

Version:

Tegera® 8801 Infinity. Multi-purpose gloves of the Infinity range with outstanding touch sensitivity and good grip capability. Particularly thin coating with nitrile foam and water-based PU coating, suitable for dry and slightly humid working areas, with oil- and grease-resistant palms. Resistant to **contact heat up to 100 °C.**

Standard:

EN 388; EN ISO 21420

EN 407

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|-----------------------|----------------------|
| Protection category | Category II |
| Type of glove | Multi-purpose gloves |
| Contents | 6 |
| Glove characteristics | Foodstuffs certified |

| | |
|--------------------|------------------------|
| EN 388 | 4121X |
| EN 407 | X1XXXX |
| Backing material | Nylon Spandex |
| Coating | Nitrile foam |
| Coating variant | The palms of the hands |
| Application range | Precision |
| Colour | black / yellow |
| Knitted technology | 15G |
| Standard | EN 407 |
| Contact heat up to | 100 °C |
| Application | reusable |
| Type of product | Multi-purpose gloves |