



Cordless combi drill, Type: 7113236H3



Order data

| | |
|--------------|------------------|
| Order number | 070100 7113236H3 |
| GTIN | 2050002046450 |
| Item class | 03F |

Description

Version:

2-Speed cordless combi drill with brushless motor.

- **Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.**
- **2-speed all-metal gearbox with selectable hammer drive in metal, stone and masonry.**
- **Multi-stage torque adjustment and removable drill chuck.**
- **With QuickIN all-metal drill chuck (120 Nm) with carbide-coated jaws and high clamping forces.**
- **FEIN SafetyCell technology. Protects the battery and the machine against overheating and deep discharge.**

Advantage:

FEIN SafetyCell technology.

Supplied with:

Supplied with 1 pc. QuickIN drill chuck (120 Nm), 1 pc. belt clip, 1 pc. bit garage and carrying case.

Note:

See No. 073851 – 073866 for suitable batteries and chargers.

Technical description

| | |
|---|------------------------------|
| maximum torque hard | 60 Nm |
| Motor design | Brushless |
| Type of rechargeable battery | Lithium-ion |
| typical application | Heavy Duty |
| maximum speed 1st speed | 0 - 450 min ⁻¹ |
| Number of rechargeable batteries contained | 2 |
| maximum torque soft | 32 Nm |
| maximum twist drill size Ø in wood | 50 mm |
| maximum speed 2nd speed | 2000 min ⁻¹ |
| Battery voltage | 18 V |
| Weight | 1.8 kg |
| maximum twist drill size Ø in steel | 13 mm |
| maximum vibration to EN with hammer drill function | 13 m/s ² |
| Manufacturer's designation | ASB 18 Q |
| Packaging | Carrying case |
| Battery capacity | 3 Ah |
| maximum vibration to EN without hammer drill function | < 2.5 m/s ² |
| Quick-clamping chuck range | 1.5 - 13 mm |
| maximum twist drill size Ø in concrete | 13 mm |
| suitable battery - supplier / battery type / voltage | Fein type E 18 V |
| Power supply | Rechargeable battery-powered |
| Suitable for material | Concrete |
| Suitable for material | Stone |
| Suitable for material | Masonry |
| Type of product | limpact drill /screwdriver |

Accessories

| | |
|--|-------------------|
| Accessories for drill / driversQuick-In Type HOLES AW | 070208 HOLES AW |
| Accessories for drill / driversQuick-In Type INCH12 | 070208 INCH12 |
| Li-ion battery Rechargeable battery type, battery voltage FE18 V | 073837 FE18 |
| Accessories for drill / driversQuick-In Type CHUCK120 | 070208 CHUCK120 |
| Li-ion battery Rechargeable battery type, battery voltage FE18 V | 073835 FE18 |
| Accessories for drill / driversQuick-In Type CHUCK60 | 070208 CHUCK60 |
| Accessories for drill / driversQuick-In Type CHUCK-SKE | 070208 CHUCK-SKE |
| Accessories for drill / driversQuick-In Type 711301 | 070208 711301 |
| Li-ion batteryHighPower Battery type, battery voltage FE18 V | 073834 FE18 |
| Offset screwdriving attachment Type OSD2 | 073920 OSD2 |
| Accessories for drill / driversQuick-In Type THREAD-SET | 070208 THREAD-SET |
| Offset screwdriving attachment Type WB1 | 073920 WB1 |
| Accessories for drill / driversQuick-In Type INCH14 | 070208 INCH14 |
| Accessories for drill / driversQuick-In Type ANGLE | 070208 ANGLE |
| Cordless combi drill Type 71132364 | 070100 71132364 |
| Battery starter set Type 92604324 | 073832 92604324 |