

**KÄRCHER****Dry ice cleaning device, Type: IB10/8L2P****Order data**

Order number	078573 IB10/8L2P
GTIN	4054278294247
Item class	07C

**Description****Version:**

Flexible cleaning with dry ice to remove obstinate dirt. Small and ergonomic blasting pistol, ideal for restricted spaces.

**Application:**

The device is portable and equipped for **integral dry ice production**. It permits cleaning work even on complex substrates, machines, motors and parts. Due to its low consumption of compressed air it is ideal for use with workshop compressors.

**Supplied with:**

IB 10/8 L2P dry ice cleaner with 5 m spray hose, spray gun, nozzle illumination, CO2 connecting hose, flat spray nozzle.

**Note:**

CO2 bottle not supplied. CO2 specifications: Standard CO2 bottle with riser tube/dip tube.

Power consumption: 1500 W

Working pressure: 0.7 – 10 bar

Air flow volume: 4200 - 48000 l/h

Weight: 92 kg

**Technical description**

Width	440 mm
Length	845 mm
Height	938 mm
Power consumption	1500 W
Manufacturer's designation	IB 10/8 L2P
Working pressure	0.7 – 10 bar
Weight	92 kg
Air flow volume	4200 - 48000 l/h
Power supply	Mains operated
Type of product	Dry ice cleaner