



Four-speed hand drill, Type: 720251



Order data

Order number	075156 720251
GTIN	4014586889849
Item class	03F

Description

Version:

Universal **four-speed hand drill** for drilling holes up to 32 mm. Reversible, speed pre-set, MT3 tool arbor for heavy-duty drilling operations.

Advantage:

For heavy work.

Note:

suitable magnetic drill stands available on request.
Suitable jobber drills can be found from No. 114000.

Technical description

maximum twist drill size \varnothing in steel 2nd speed	20 mm
Manufacturer's designation	BOZ 32-4 M
Weight	7.5 kg
Maximum twist drill size \varnothing in steel 1st speed	32 mm
Power consumption	1800 W
Speed range 2nd speed	0 - 480 min ⁻¹
maximum twist drill size \varnothing in wood 1st speed	60 mm

maximum vibration to EN	<2.5 m/s ²
maximum twist drill size Ø in wood 2nd speed	70 mm
Speed range 1st speed	0 - 140 min ⁻¹
Drill chuck adapter	MT3
Power supply	Mains operated
Suitable for material	Steel
Type of product	Drill