

ejendals

Pair of cold protection gloves Tegera® 517, Glove size: 10



Order data

Order number	094824 10
GTIN	7392626070707
Item class	04R

Description

Version:

Tegera® 517. **Waterproof** and **lined** cold protection gloves of **synthetic leather** for precision work on activities in cold and wet environments. With hook and loop fastening and reinforced finger tips.

Version of the advertising text:

Tegera® 517. **Waterproof** and **lined** cold protection gloves of **synthetic leather** for precision work on activities in cold and wet environments. With hook and loop fastening and reinforced finger tips.

Application:

For windy, cold or wet working conditions.

Use of the advertising text:

For windy, cold or wet working conditions.

Standard:

EN 388; EN 511

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. Particularly closely cut. Equivalent to one size smaller.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Particularly closely cut. Equivalent to one size smaller.

Technical description

Protection category	Category II
Glove size	10
Type of glove	Cold protection gloves
Glove characteristics	Hook & loop fastener
Contents	6
Application	reusable
Application range	All-round
Application range	Heavy Duty
Standard	EN 511
Length	235 mm
EN 388	1121X
EN 511	111
Backing material	Polyester/synthetic leather
Coating variant	No coating
Colour	black / green
Type of product	Cold protection gloves