

Garant
Plug-in ratchet reversible, Type-Square drive: 1-1/2in

Order data

Order number	657582 1-1/2
GTIN	4062406277291
Item class	61E

Description
Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench. Very compact **plug-in reversible ratchet with ejector**.

Material:

Chrome vanadium steel, chrome-plated.

Cutting dataa:
Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Further plug-in heads with rectangular plug-in shank 22 × 28 mm available on request.

Technical description

Plug-in shank	9×12 mm
Height h	16.4 mm
Long-term rated loading	135 Nm
Pitch S	28 mm
Square drive	1/2 in
Width b	32 mm
No. of teeth	48
Exchangeable tool	Plug-in head
Material	Chrome vanadium steel
Surface	chrome-plated
Ratchet reversible	yes
Ratchet with ejector	yes
Type of product	Ratchet