

**Garant****Open jaw plug-in head, Type-Width across flats: 2-22mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 657792 2-22   |
| GTIN         | 4062406277499 |
| Item class   | 61E           |

**Description****Version:**

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

**Material:**

Chrome vanadium steel, chrome-plated.

**Cutting dataa:****Legend for drawing and formula:**

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

L = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

**Suitable for:**

Torque wrench with rectangular sockets.

**Note:**

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

## Technical description

|                    |                             |
|--------------------|-----------------------------|
| Plug-in shank      | 14×18 mm                    |
| Height h           | 11 mm                       |
| Width b            | 47.3 mm                     |
| Pitch S            | 25 mm                       |
| Width across flats | 22 mm                       |
| Exchangeable tool  | Plug-in head                |
| Material           | Chrome vanadium steel       |
| Surface            | chrome plated (non-flaking) |
| Type of product    | Open ended plug-in head     |