

Garant**Open jaw plug-in head, Type-Width across flats: 1-8mm****Order data**

| | |
|--------------|---------------|
| Order number | 657792 1-8 |
| GTIN | 4062406277314 |
| Item class | 61E |

Description**Version:**

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Material:

Chrome vanadium steel, chrome-plated.

Cutting dataa:**Legend for drawing and formula:**

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Technical description

| | |
|--------------------|-----------------------------|
| Width b | 22 mm |
| Height h | 5.7 mm |
| Plug-in shank | 9×12 mm |
| Width across flats | 8 mm |
| Pitch S | 17.5 mm |
| Exchangeable tool | Plug-in head |
| Material | Chrome vanadium steel |
| Surface | chrome plated (non-flaking) |
| Type of product | Open ended plug-in head |