

Garant GRIDLINE

Auxiliary cabinet with cupboard, for individual configuration with drawers, 20×24G, Height mm: 800**Order data**

Order number	932012 800
GTIN	4062406277024
Item class	9GK

Description**Version:**

Tool auxiliary cabinet in 24×28G, with drawers 20×24G. Cupboard with door and storage shelf, adjustable in 25 mm intervals. Door separately lockable by push handle with cylinder lock.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Door height	450 mm
Width	600 mm
Drawer usable width in G	20
Drawer usable area in G	20×24

Height	800 mm
Weight	59 kg
Drawer usable depth in G	24
Depth	700 mm
Usable height	700 mm
Usable height for drawers	250 mm
Drawer usable width	500 mm
Drawer usable depth	600 mm
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Shelf load capacity / maximum distributed shelf load (on metal)	80 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
Slide handle for GridLine Type HU12	914226 HU12