

Garant GRIDLINE

**Swing-door auxiliary cabinet without raised edge, 26×20G, Height: 800mm****Order data**

Order number	932101 800
GTIN	4062406277055
Item class	9GK

**Description****Version:**

Tool auxiliary cabinet 30×28G. With swing doors, can be locked centrally with a cylinder lock. An anti-tilt device prevents more than one drawer being opened at one time.

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body and storage shelf not configurable, always RAL 7035 light grey.**

**Note:**

Suitable drawers 26×20G.

**Technical description**

Depth	700 mm
Width	750 mm
Weight	42 kg
Usable height	650 mm
Height	800 mm
Material thickness	1.2 mm

Drawer runner extension	Anti-tilt lock
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x20G
Type of product	Machine auxiliary cabinet

---

## Accessories

Slide handle for GridLine Type HU12	914226 HU12
-------------------------------------	-------------