



Ceiling and assembly support, maximum length: 250cm



Order data

Order number	861780 250
GTIN	4008158041254
Item class	83K

Description

Version:

Extremely stable structure thanks to high-tensile steel pipe and non-slip PVC contact surfaces. Single-handed operation thanks to 2-component plastic handle with pump mechanism. Pushbutton for quick extension and retraction of the telescopic rod. Holding force adjustable by twisting the support on the grip. Up to **maximum 160 kg (size 250) or 110 kg (size 300) load capacity when the telescopic rod is fully retracted**. The contact surfaces can also be **pivoted steplessly** for use at angles **-45° to 45°**.

When used at an angle, load capacity is limited to max. 40 kg.

Application:

For fixing plasterboard, wooden boards, panels, roof laths, metal strips, foils and luminaires at a height of up to 3.00 m. Can also be used without problems at angles due to the pivoted and non-slip PVC contact surfaces.

Technical description

Pivot angle	-45 - 45 degrees
maximum load capacity	160 kg

Material of handle	2-component plastic
Material	Steel
Special features	can be tilted
Special features	non-slip
overall length	145 - 250 cm
suitable for	Roof laths
suitable for	Lamp bodies
suitable for	Panels
suitable for	Plasterboard
suitable for	Foils
suitable for	Wooden boards
suitable for	Metal strips
Carrier plate	9×7 cm
Weight	3.1 kg
Type of product	Ceiling support / assembly support