



## Plug-in ratchet, Type-Square drive: 1-3/8in



### Order data

|              |               |
|--------------|---------------|
| Order number | 657630 1-3/8  |
| GTIN         | 4062406278335 |
| Item class   | 62E           |

### Description

#### Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

#### Plug-in reversible ratchet.

#### Material:

Chrome vanadium steel, chrome-plated.

#### Cutting dataa:

#### Legend for drawing and formula:

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

L = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

#### Suitable for:

Torque wrench with rectangular sockets.

#### Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Further plug-in heads with rectangular plug-in shank 22 × 28 mm available on request.

## Technical description

|                         |                       |
|-------------------------|-----------------------|
| Pitch S                 | 17.5 mm               |
| Long-term rated loading | 135 Nm                |
| No. of teeth            | 52                    |
| Plug-in shank           | 9×12 mm               |
| Height h                | 22.5 mm               |
| Square drive            | 3/8 in                |
| Width b                 | 35 mm                 |
| Exchangeable tool       | Plug-in head          |
| Material                | Chrome vanadium steel |
| Ratchet reversible      | yes                   |
| Ratchet with ejector    | no                    |
| Type of product         | Ratchet               |