

**Garant**
**Square Drive Insert, Type-Square drive: 1-3/8in**

**Order data**

Order number	657698 1-3/8
GTIN	4062406278380
Item class	61E

**Description**
**Version:**

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

**Square plug-in head.**
**Material:**

Chrome vanadium steel, chrome-plated.

**Cutting dataa:**
**Legend for drawing and formula:**

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

L = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

**Suitable for:**

Torque wrench with rectangular sockets.

**Note:**

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Further plug-in heads with rectangular plug-in shank 22 × 28 mm available on request.

---

## Technical description

Width b	23 mm
Plug-in shank	9×12 mm
Long-term rated loading	135 Nm
Pitch S	17.5 mm
Square drive	3/8 in
Height h	15 mm
Exchangeable tool	Plug-in head
Material	Chrome vanadium steel
Type of product	Square drive plug-in head